

メーカー	システム	径タイプ	嵌合形式		歯肉貫通部長さ(カフ)						ベース高さ	フレア
			エンゲージ	ノンエンゲージ	0.5mm	1mm	2mm	3mm	4mm	5mm	mm	mm
ZimVie	Spline	3.25	○	○	○	-	-	-	-	-	H4.2/H5/H7.5	4.4
			○	○	-	○	-	-	-	-	H3.7/H5/H7.5	4.4
			○	○	-	-	○	○	○	○	H3/H5	3.85
			○	○	-	-	○	○	○	○	H7.5	4.4
		○	○	○	-	-	-	-	-	H4.2/H5/H7.5	5.0	
		○	○	-	-	-	-	-	-	H3.7/H5/H7.5	5.0	
		○	○	-	-	○	○	○	○	H3/H5	3.85	
		○	○	-	-	○	○	○	○	H7.5	4.0	
		○	○	○	-	-	-	-	-	H4.2/H5/H7.5	5.0	
		○	○	-	○	-	-	-	-	H3.7/H5/H7.5	5.0	
		○	○	-	-	○	○	○	○	H3/H5/H7.5	5.0	
		○	○	○	○	○	○	○	○	H3/H5	4.0	
	ScrewVent	3.5	○	○	○	○	○	○	○	○	H7.5	4.3
			○	○	○	○	○	○	○	○	H3/H5	4.5
			○	○	○	○	○	○	○	○	H7.5	4.7
		4.5	○	○	○	○	○	○	○	○	H3/H5/H7.5	5.7
			○	○	○	○	○	○	○	○	H3/H5	3.85
			○	○	○	○	○	○	○	○	H7.5	4.3
	Certain Internal	3.4	○	○	○	○	○	○	○	○	H3/H5	4.1
			○	○	○	○	○	○	○	○	H7.5	4.3
○			○	○	○	○	○	○	○	H3/H5	4.1	
4.1		○	○	○	○	○	○	○	○	H7.5	4.3	
		○	○	○	○	○	○	○	○	H3/H5/H7.5	5.0	
		○	○	○	○	○	○	○	○	H3/H5/H7.5	6.0	
straumann	Bone Level	NC	○	○	○	○	○	○	○	○	H3/H5	4.0
			○	○	○	○	○	○	○	○	H7.5	4.2
		RC	○	○	○	○	○	○	○	○	H3/H5	4.5
			○	○	○	○	○	○	○	○	H7.5	4.6
	BLX	RB	○	-	-	○	○	○	○	-	H3/H5	3.9
			-	-	-	-	-	-	-	-	-	-
		WB	○	○	○	○	○	○	○	○	H3/H5	4.0
			○	○	○	○	○	○	○	○	H7.5	4.3
Nobel Biocare	NobelActive	NP	○	○	○	○	○	○	○	○	H3/H5	4.0
			○	○	○	○	○	○	○	○	H7.5	4.3
	Nobel Tapered CC	RP	○	○	○ <small>カフ0.6mm</small>	○	○	○	○	○	H3/H5	4.3
			○	○	○ <small>カフ0.6mm</small>	○	○	○	○	○	H7.5	4.8
ALTADENT	Camlog	3.3	○	○	○	○	○	○	○	○	H3/H5	4.0
			○	○	○	○	○	○	○	○	H7.5	4.2
		3.8	○	○	○	○	○	○	○	○	H3/H5	4.0
			○	○	○	○	○	○	○	○	H7.5	4.2
		4.3	○	○	○	○	○	○	○	○	H3/H5	4.5
			○	○	○	○	○	○	○	○	H7.5	4.5
	Conelog	5.0	○	○	○	○	○	○	○	○	H3/H5/H7.5	5.0
			○	-	-	○	○	○	○	○	H3/H5	4.0
		3.8	○	-	-	○	○	○	○	○	H3/H5	4.0
			○	-	-	○	○	○	○	○	H3/H5	4.3
BIOHORIZONS	Internal	3.0	○	-	○	○	○	○	○	○	H3/H5	4.3
			○	-	○	○	○	○	○	○	H7.5	4.5
		3.5	○	-	○	○	○	○	○	○	H3/H5	4.5
			○	-	○	○	○	○	○	○	H7.5	4.5
		4.5	○	-	○	○	○	○	○	○	H3/H5	4.7
			○	-	○	○	○	○	○	○	H7.5	4.9
		5.7	○	-	○	○	○	○	○	○	H3/H5/H7.5	5.9
			○	-	○	○	○	○	○	○	H3/H5	4.4
Dentsply Sirona	OsseoSpeed TX	Aqua	○	○	○ <small>カフ0.6mm</small>	○	○	○	○	○	H3/H5	4.4
			○	○	○ <small>カフ0.6mm</small>	○	○	○	○	○	H7.5	4.7
		Lilac	○	○	○ <small>カフ0.6mm</small>	○	○	○	○	○	H3/H5	4.4
			○	○	○ <small>カフ0.6mm</small>	○	○	○	○	○	H7.5	4.7
	EV	3.6	○	-	○	○	○	○	○	○	H3/H5	4.2
			○	-	○	○	○	○	○	○	H7.5	4.5
		4.2	○	-	○	○	○	○	○	○	H3/H5	4.4
			○	-	○	○	○	○	○	○	H7.5	4.7
4.8	○	-	○	○	○	○	○	○	H3/H5	4.5		
	○	-	○	○	○	○	○	○	H7.5	4.8		
5.4	○	-	○	○	○	○	○	○	H3/H5	5.4		
	○	-	○	○	○	○	○	○	H7.5	5.4		
Dentium	SuperLine	共通	○	○	○	○	○	○	○	○	H3/H5	4.2
			○	○	○	○	○	○	○	○	H7.5	4.4
KYOCERA	FINESIA BONE LEVEL ※	共通	○	○	○	○	○	○	○	○	H3/H5	3.8
			○	○	○	○	○	○	○	○	H3/H5	4.1
			○	○	○	○	○	○	○	○	H3/H5	4.6
Megagen	AnyOne	共通	○	○	○	○	○	○	○	○	H3/H5	4.2
			○	○	○	○	○	○	○	○	H7.5	4.4
	AnyRidge	共通	○	○	○	○	○	○	○	○	H3/H5	4.2
			○	○	○	○	○	○	○	○	H7.5	4.4
OSSTEM	TS	Mini	○	○	○	○	○	○	○	○	H3/H5	4.1
			○	○	○	○	○	○	○	○	H7.5	4.4
		Regular	○	○	○	○	○	○	○	○	H3/H5	4.2
			○	○	○	○	○	○	○	○	H7.5	4.4

※ スクリューは付属しません。別途、純正スクリューをご購入ください。